

HAFFMANS c-TPO INPACK TPO/CO₂ METER

PRODUCT LEAFLET



GENERAL PRODUCT INFORMATION

In the beer and beverage industries both oxygen (O_{a}) and carbon dioxide (CO_{a}) are important gases. When it comes to product life and flavor stability, oxygen is detrimental. Preventing O₂ pick-ups during the entire production and packaging process is of paramount importance. As a result, beer and beverages are produced with very low dissolved oxygen (DO) levels, to achieve consistent quality and high flavor stability during the product's shelf life. The content of dissolved CO₂ is decisive to the quality and taste of beer and carbonated beverages. Therefore, brewers and beverage manufacturers continuously control and measure the CO₂ content in bottled and canned beverages.

The automatic Inpack TPO/CO₂ Meter, type c-TPO meets the demands. The differentiated measurement of headspace O_2 and DO provides immediate insight in the performance of the filling operation. The multiple routine determinations of TPO and CO₂ are fully automated. Up to 150 different product types/packages can be programmed and easily selected. The instrument is suited for the most common sizes of bottles and cans.

Beyond traditional TPO measurement methods and instruments, the c-TPO measures the headspace O_2 and DO by the filler, while at the same time the liquid remains in the package and is not consumed by the instrument. Sample preparation time is skipped and lab space is minimized. The c-TPO also supports the well-known z-factor method according to Uhlig. The CO₂ content is measured according to Henry's Law.

BENEFITS

- High quality beer and beverages in every package
 - prevent inferior product entering the market
 - save time and money and maximize the ROI
 - no sample preparation
 - fully automated measurement
- All-in-one measurement: HSO, DO, TPO and CO,
 - reduce process downtime
 - prevent product losses
 - low maintenance

APPLICATIONS

- Laboratory, applicable in breweries and soft drink industries
- Filling department, applicable in breweries and soft drink industries

HAFFMANS c-TPO INPACK TPO/CO, METER

PRODUCT LEAFLET





TECHNICAL DATA

Measuring range

TPO, HSO, DO, Headspace Volume, CO₂, Temperature, Pressure

Measuring range

 Oxygen content
 0.00 - 4.18%

 D0 value
 0.000 - 2.000 mg/l

 C02 value
 2.0 - 15.0 g/l

 HS volume
 0.0 - 500 ml

 Temperature
 -5.0 - 40.0 °C

 Pressure0.00 - 5.00 barg
 -5.00 barg

Accuracy

D0 value $\pm (1 \text{ ppb} + 2\% \text{ m.v.})^*$ C0₂ value $\pm 0.1 \text{ g/l}$ Temperature $\pm 0.2 \text{ °C}$ Pressure $\pm 0.02 \text{ bar}$

Memory capacity

Up to 250 measurements

Bottle dimensions

Height min. 90 mm - max. 440 mm Diameter min. 55 mm - max. 200 mm

Can dimensions

Height min. 80 mm - max. 195 mm Diameter min. 50 mm - max. 73 mm

Voltage

80-240 V / AC 50-60 Hz

Interface USB, barcode reader

Dimensions

max. 550 x 330 x 1120 (LxWxH mm) min. 550 x 330 x 680 (LxWxH mm)

Weight 40 kg

* at 20 °C

SCOPE OF SUPPLY

- Inpack TPO/CO, Meter, type c-TPO
- Mains cable (Euro, US, UK or AUS plug)
- Service set with piercers and sealing rubbers
- Software set (CD + Interface cable)
- Instruction manual

OPTIONS

- Certificate of measurement
- PET bottle holder
- Barcode reader





HAFFMANS BV

P.O. BOX 3150 NL-5902 RD VENLO, NETHERLANDS INFO@HAFFMANS.NL WWW.HAFFMANS.NL

All Pentair trademarks and logos are owned by Pentair. All other brand or product names are trademarks or registered marks of their respective owners. Because we are continuously improving our products and services, Pentair reserves the right to change specifications without prior notice. Pentair is an equal opportunity employer.

c-TPO E-7 /14 © 2014 Pentair. All Rights Reserved.